

Parameter	
Tip Hardness	30HRC
Amplitude	20-60µm
Treatment Depth	14mm
Power Input	100V-240V 50/60HzL.2A(Max)
Input Power	48VA
Tip Offset	1µm100µm Root Canal
Tip Offset	<1mm
Half Offset Force	0.1N2N
Operating Frequency	2040kHz
Circuit Board Fuse	F1.6AL250V
Main Unit Fuse	T0.5AL250V
Dimensions	290mmx168mmx155mm

Xpedent Scaler Machine

SHEL-P



Follow up

- 
 Yang Jenny
- 
 Xpedent International
- 
 xpedent_international
- 
 jenny@xpedent.com

- 

Xpedent Head Office

Xpedent UK LTD

The Old Granary
West Chilington
West Sussex
RH20 2JY England
- 

Sales office

Xpedent Austria GmbH

Millennium Park 9
6890 Lustenau
Austria
- 

R & D Center

Alpazat holdings Limited

Unit C, 16/F.,
World Trust Tower
No. 50 Stanley Street
Central
Hong Kong
- 

Manufacturer

GUILIN YIKESHI MEDICAL
INSTRUMENT CO., LTD

D08 Building, High Tech Industrial Park,
Chaoyang Road, Qixing District Guilin,
541004, China



SHEL-P



Autoclave box × 1




Handpiece × 1



Torque Wrench × 1



Pedal × 1



6 Tips

Option for specialized medication Drip-prevention design to meet clinical needs

Water control knob with Inductive and Detachable function Hygienic and safe Automatic cleaning function incorporated

Double Anti-Bend Designed Handpiece with long life span

Freely switched built-in and external water supply



Quick release for handpiece cable of external dental unit to connect to the dental unit foot pedal conveniently and quickly

Sensitive Touch Control Plate with Hygienic Reliable, Waterproof and Durable quality

Led handpiece

Detachable Metal Handpiece High temperature and pressure sterilization available

